

## Eaton TMC3-075-2

Eaton Crouse-Hinds series TMC3 cable gland, 0.800" - 1.120" armor min./max., 0.850" - 1.310" cable range min./max., Armoured and non-armoured, Aluminum, 0.850" - 1.310" outer sheath min./max., Industrial protection, 3/4" NPT

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series TMC3 cable gland
<b>CATALOG NUMBER</b>	TMC3-075-2
<b>UPC</b>	662277129923
<b>PRODUCT LENGTH/DEPTH</b>	4.97 in
<b>PRODUCT HEIGHT</b>	1.99 in
<b>PRODUCT WIDTH</b>	1.99 in
<b>PRODUCT WEIGHT</b>	0.64 lb

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Hazardous/Classified Locations
<b>STANDARDS TYPE</b>	NEC/CEC IECEX/ATEX
<b>NEC HAZARDOUS RATING</b>	Class II, Division 1 Class III
<b>NEMA RATING</b>	4X
<b>INGRESS PROTECTION (IP) RATINGS</b>	IP66

## Product specifications

<b>PROTECTION TYPE</b>	Industrial
<b>GLAND TYPE</b>	Armoured and non-armoured
<b>CABLE TYPE</b>	MC
	MC-HL
	TECK
	TC
	TC-ER
	TC-ER-HL
	ITC
	ITC-ER
	ITC-HL
	PLTC
	PLTC-ER
	ACIC
<b>MATERIAL</b>	Aluminum
<b>THREAD SIZE</b>	3/4"
<b>THREAD TYPE</b>	NPT
<b>ARMOR (MIN/MAX)</b>	0.800" - 1.120"
<b>CABLE RANGE (MIN/MAX)</b>	0.850" - 1.310"
<b>OUTER SHEATH (MIN/MAX)</b>	0.850" - 1.310"

[IF 1890 - TMC3 Cable Gland](#)

[Crouse-Hinds series TMC3 Armored Gland brochure](#)

[Crouse-Hinds series TMC3 Armored and Non-armored Cable Glands catalog page](#)

[TMC3 Armored Gland UL certification \(Zones\)](#)

[TMC3 Armored Gland UL certification \(Class and Division\)](#)

[TMC3 Armored Gland ATEX/IECEX certification](#)

[TMC3 Armored Gland Canadian certification \(Zones\)](#)

[TMC3 Armored Gland Canadian certification \(Class and Division\)](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

