



□□□□□

Eaton TMC8302

Eaton Crouse-Hinds series TMC cable gland, Metal-clad, TECK corrugated or interlocked steel, or aluminum, Armoured, Aluminum, Outer sheath: 2.52-3.28", General purpose, 3" NPT, Armor range: 2.45-3.02"

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series TMC cable gland
CATALOG NUMBER	TMC8302
UPC	782274414621
PRODUCT LENGTH/DEPTH	6.32 in
PRODUCT HEIGHT	4.88 in
PRODUCT WIDTH	4.88 in
PRODUCT WEIGHT	4.4 lb

Certifications and compliances	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4

Product specifications	
PROTECTION TYPE	General purpose
CABLE TYPE	Metal-clad, TECK corrugated or interlocked steel, or aluminum
GLAND TYPE	Armoured
MATERIAL	Aluminum
THREAD SIZE	3"
THREAD TYPE	NPT
ARMOR (MIN/MAX)	2.45-3.02"
OUTER SHEATH (MIN/MAX)	2.52-3.28"

Links	
IF 1183	IF 1183 - Terminator Cable Fittings
Eaton Specification Sheet - TMC8302	Eaton Specification Sheet - TMC8302
Crouse-Hinds series TMC catalog page	Crouse-Hinds series TMC catalog page
TMC Armoured Gland UL certification	TMC Armoured Gland UL certification

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: