




Eaton U009-010-RJ45-X

USB-A to RJ45 Rollover Console Cable (M/M)
- Cisco Compatible, 250 Kbps, 10 ft. (3.05 m),
Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U009-010-RJ45-X
UPC	037332222114
PRODUCT LENGTH/DEPTH	10 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.31 lb
COMPLIANCES	CE Marked FCC Compliant REACH RoHS

TYPE	USB 1.1 (up to 12 Mbps)
COLOR	Black
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	U009-010-RJ45-X USB to RJ45 Rollover Console Cable (M/M), Black, 10-ft. (3.05 m)
SYSTEM REQUIREMENTS	USB Cat5/5e Windows (up to 11), Mac (up to 10.12), or Linux (up to Redhat 9.0) operating systems Serial-based Cisco device with console port Computer or laptop with USB-A port
CONNECTOR TYPE	Networking-copper USB/Thunderbolt/Lightning
PRODUCT FEATURES	Suspend Mode Support Driver Required
USB SPECIFICATION	USB 1.1 (up to 12 Mbps)
CABLE JACKET MATERIAL	PVC
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Great for programming, resetting or rebooting a Cisco switch, firewall, router or modem Double-shielded construction cuts crosstalk and EMI/RFI line noise Compatible with Windows, Mac and Linux Plug-and-play operation with no software required for easy, immediate installation 10-ft. (3.05 m) cable supports data transfer speeds up to 250 Kbps
PACKAGING TYPE	Polybag
SIDE A CONNECTOR1	USB A (MALE)
SIDE B CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR3	RJ45 (MALE)
HOST CONNECTOR	USB A (MALE)
TECHNOLOGY	Cat5/5e USB
FEATURES	Flex Center
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)



RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
AWG-SIZE	26
CABLE LENGTH	10 Foot
MATERIAL OF CONSTRUCTION	PVC, PE
OUTER CABLE DIAMETER	5.5mm; 4.7mm +/- 0.15
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
CONNECTOR GROUP	USB-A RJ45
CONNECTOR	RJ45 (male) USB A (male)
