



Eaton U040-006-C-5A

USB-C Cable (M/M) - USB 2.0, 5A (100W)
Rated, 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U040-006-C-5A
UPC	037332202871
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.08 lb
COMPLIANCES	RoHS FCC Compliant CE Marked REACH

□□□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	USB 2.0 Hi-Speed Cable with 5A Rating, USB-C to USB-C (M/M), 6 ft.
PRODUCT HIGHLIGHTS	Backward compatible with previous USB generations Supports data transfer speeds up to 480 Mbps 3-year limited warranty (Worldwide) Integral strain relief protects against stress and cracking Power output up to 5A for fast-charging large mobile devices Reversible USB-C plugs on both ends for fumble-free connection
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB C (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
CABLE LENGTH	5 - 8ft (1 - 2M)
CABLE OUTER DIAMETER (OD)	4.0MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C
MATERIAL	PVC
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CONNECTOR	USB C (male)

□□	
----	--

