



Eaton U050-003

USB 2.0 A to Micro-B Cable (M/M), 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U050-003
UPC	037332147974
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.07 lb
COMPLIANCES	RoHS



Powering Business Worldwide



OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR TYPE	USB/Thunderbolt/Lightning
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	3-ft. (0.91 m) USB 2.0 A-Male to Micro-B Male
PRODUCT HIGHLIGHTS	Standard "A" Male to Micro-B Male Next Generation USB Digital Device Connector Provides both Data and Power transfers USB 2.0 480Mbps Transfer rates
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	MICRO-USB B (MALE)
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
SIDEB CONNECTOR3	MICRO-USB B (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A Micro USB
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB A (male) Micro USB-B (male)

