



Eaton U209-006-RJ45XC

USB-C to RJ45 Serial Rollover Cable (M/M) -
Cisco Compatible, 250 Kbps, 6 ft. (1.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U209-006-RJ45XC
UPC	037332268655
PRODUCT LENGTH/DEPTH	4.13 in
PRODUCT HEIGHT	1.22 in
PRODUCT WIDTH	4.65 in
PRODUCT WEIGHT	0.242 lb
COMPLIANCES	REACH CE Marked FCC Compliant RoHS
CERTIFICATIONS	EN 55032 EN 55035



Powering Business Worldwide



OPERATING HUMIDITY RANGE	0% TO 90% RH, NON-CONDENSING
STORAGE HUMIDITY RANGE	0% TO 90% RH, NON-CONDENSING
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Blue
CONNECTOR COLOR	Black
CONNECTOR TYPE	USB/Thunderbolt/Lightning Networking-copper
PRODUCT FEATURES	Driver Required Remote Wakeup Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	250 Kbps
PACKAGE CONTENTS	Owner's manual U209-006-RJ45XC USB-C to RJ45 Serial Rollover Cable, M/M, 6 ft. (1.8 m)
PRODUCT HIGHLIGHTS	Compatible with Windows, macOS and Linux operating systems, as well as Eaton's G4 PDU Network Card Supports data transfer rates up to 250 Kbps Designed for Cisco equipment with no adapters or external power required Premium double-shielded cable eliminates crosstalk and reduces EMI/RFI interference Supports remote wake-up and power management
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Serial USB
NETWORK	250 Kbps



