



## Eaton U263-AC600

Dual-Band USB Wi-Fi Adapter - 2.4 GHz and 5 GHz



<b>PRODUCT NAME</b>	Eaton Tripp Lite series USB adapter
<b>CATALOG NUMBER</b>	U263-AC600
<b>UPC</b>	037332259738
<b>PRODUCT LENGTH/DEPTH</b>	3.2 in
<b>PRODUCT HEIGHT</b>	0.75 in
<b>PRODUCT WIDTH</b>	2.6 in
<b>PRODUCT WEIGHT</b>	0.34 lb
<b>COMPLIANCES</b>	REACH RoHS CE Marked FCC Compliant



Powering Business Worldwide



<b>SPECIAL FEATURES</b>	5% to 90% RH, Non-Condensing
<b>TYPE</b>	USB 2.0 Dual Band 2.4Ghz / 5Ghz Wi-Fi Adapter
<b>COLOR</b>	Black
<b>PACKAGE CONTENTS</b>	U263-AC600 Dual-Band USB Wi-Fi Adapter Owner's manual
<b>SYSTEM REQUIREMENTS</b>	Wireless USB 2.0 (High Speed) Windows, Mac or Linux operating system 2.4 GHz and/or 5 GHz wireless network Laptop, tablet or desktop computer with USB-A port
<b>CONNECTOR TYPE</b>	USB/Thunderbolt/Lightning Networking-copper
<b>PRODUCT FEATURES</b>	Driver Required Bus Powered Network (Ethernet) Protection
<b>USB SPECIFICATION</b>	USB 2.0 (up to 480 Mbps)
<b>PRODUCT HIGHLIGHTS</b>	Dual-band Wi-Fi adapter supports 2.4 GHz and 5 GHz networks Supports 64- and 128-bit WEP/WPA and WPA2 wireless security encryption 802.11 ac adapter is backward compatible with 802.11 a, 802.11b, 802.11g and 802.11n USB 2.0 host interface is backward compatible with USB 1.1 laptops, tablets and PCs Nano-sized 1T1R design fits easily into a pocket or laptop bag for connecting on the go
<b>PACKAGING TYPE</b>	Box
<b>SIDE A CONNECTOR1</b>	USB A (MALE)
<b>TECHNOLOGY</b>	Wireless USB 2.0 (High Speed)
<b>FEATURES</b>	Flex Center
<b>OPERATING HUMIDITY</b>	10% to 90% RH, Non-Condensing
<b>OPERATING TEMPERATURE RANGE</b>	32° to 104°F (0° to 40°C)

