



Eaton U264-001-APL

Wireless Apple CarPlay Adapter for Vehicles,
Apple iPhone Compatible, Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U264-001-APL
UPC	037332292308
PRODUCT LENGTH/DEPTH	1.57 in
PRODUCT HEIGHT	0.55 in
PRODUCT WIDTH	2.32 in
PRODUCT WEIGHT	0.15 lb
COMPLIANCES	CE Marked FCC Class B REACH RoHS UKCA WEEE Directive
CERTIFICATIONS	EN 55032 CISPR 35/EN 55035 ICES



Powering Business Worldwide

□□□□	
TYPE	USB Wireless Apple Carplay Adapter
DEVICE COMPATIBILITY	Phone
OPERATING HUMIDITY RANGE	10% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 95% RH, Non-Condensing
COLOR	Black
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	Bus Powered
CABLE JACKET MATERIAL	TPE
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U264-001-APL Wireless Apple CarPlay Adapter Installation instructions USB-A to USB-C adapter
PRODUCT HIGHLIGHTS	Compatible with Apple iPhone 6 or later models that are on iOS 10 and above Included USB adapter allows connection with your vehicle's USB-A or USB-C port Recommended for daily travel use, especially sales pros who are always on the go Reduces cable clutter in your vehicle while enabling music, navigation, Siri control and more Plug-and-play operation with no software required for easy, immediate installation 3-year limited warranty (Worldwide)
POWER SOURCE TYPE	Bus
SIDEA CONNECTOR1	USB A (MALE)
OPERATING TEMPERATURE	32° to 122°F (0 to 50°C)
OPERATING TEMPERATURE RANGE	32° to 122°F (0 to 50°C)
STORAGE TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)
HOST CONNECTOR	USB A (MALE)

□□

TECHNOLOGY	USB Wireless
BUILT-IN CABLE LENGTH	0.33 ft
CABLE LENGTH	Up to 4ft (up to 1M)
NUMBER OF PORTS	0
NUMBER OF USB HUB PORTS	0
TOTAL NUMBER OF PORTS	0
CABLE OUTER DIAMETER (OD)	3.3MM
LED INDICATORS	(1) Connection LED: Turns blue when initially powered on before turning to green (flashes when attempting to connect to iPhone; solid when connection is established).
CONNECTOR GROUP	USB-A
MATERIAL	MAIN BODY: TEMPERED GLASS AND ALUMINUM; PCB
OVER CURRENT PROTECTION	N
WIRE GAUGE (AWG)	28
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB A (male)

□□□□:
□□□□:
□□□:
□□: