



Eaton U280-002-W12

2-Port USB Wall/Travel Charger, 5V 3.4A / 17W



PRODUCT NAME	Eaton Tripp Lite series wall charger
CATALOG NUMBER	U280-002-W12
UPC	037332188380
PRODUCT LENGTH/DEPTH	6 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	4 in
PRODUCT WEIGHT	0.001 lb
COMPLIANCES	FCC Compliant RoHS REACH CE Marked WEEE Directive
CERTIFICATIONS	UL Listed



Powering Business Worldwide



TYPE	Wall Charger
CHARGING PORTS DETAILS	USB-A: 5V 1A (5W) USB-A: 5V 2.4A (12W)
NUMBER OF CHARGING PORTS	2
TOTAL CHARGING AMPS	3.4A
TOTAL CHARGING WATTS	17
NUMBER OF PORTS	2
OVERLOAD PROTECTION	Yes
COLOR	White
INPUT PLUG TYPE	NEMA 1-15P (NON-POLARIZED)
CHARGING PORTS / AMPS	1A 2.4A
CHARGING METHOD	USB
CONNECTOR TYPE	Power USB/Thunderbolt/Lightning
INPUT NOMINAL VOLTAGE	120 VAC 230 VAC
PRODUCT FEATURES	Overcurrent Protection Overvoltage Protection
PACKAGE CONTENTS	U280-002-W12 2-Port USB Wall/Travel Charger
PRODUCT HIGHLIGHTS	Features two 5V USB-A ports: 1.0A and 2.4A Folding plug design protects plug from damage Perfectly sized for purses, suitcases, backpacks and laptop bags Automatically adjusts to ensure optimum charging speed Plugs into any NEMA 1-15R, NEMA 5-15R or NEMA 5-15/20R socket
CHARGING FORM FACTOR	Direct plug-in
CHARGING PORT TYPE	USB A (FEMALE)
SIDEA CONNECTOR1	NEMA 1-15P (NON-POLARIZED)
SIDEB CONNECTOR1	USB A (FEMALE)
SIDEB CONNECTOR3	USB A (FEMALE)
DEVICE COMPATIBILITY	Amazon Kindle Phone Tablet
VOLTAGE	100 VAC

