



Eaton U280-004-UK

4-Port USB Charging Station, 5V 6A/30W USB
Charger Output, UK Version



PRODUCT NAME	Eaton Tripp Lite series multi-device charger
CATALOG NUMBER	U280-004-UK
UPC	037332192080
PRODUCT LENGTH/DEPTH	7.3 in
PRODUCT HEIGHT	2 in
PRODUCT WIDTH	5.2 in
PRODUCT WEIGHT	0.5 lb
COMPLIANCES	CE Marked RoHS REACH FCC Compliant



Powering Business Worldwide



TYPE	Plug in Charger
CHARGING PORTS DETAILS	USB-A: 5V/6A
NUMBER OF CHARGING PORTS	4
TOTAL CHARGING AMPS	6A
TOTAL CHARGING WATTS	30
POWER CONSUMPTION DETAIL	38W (Operating) 0.26W (Standby)
POWER CONSUMPTION	38 W
NUMBER OF PORTS	4
OVERLOAD PROTECTION	Yes
CHARGING METHOD DETAIL	5V - 1.5A (7W)
INPUT CURRENT	120V (0.8A) / 230V (0.4A)
INPUT FREQUENCY	50 / 60 Hz
LED INDICATORS	Blue (Power)
OPERATING TEMPERATURE RANGE	41° to 95°F (5° to 35°C)
STORAGE TEMPERATURE RANGE	-4° to 122°F (-20° to 50°C)
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
COLOR	White
INPUT PLUG TYPE	NEMA 1-15P (NON-POLARIZED)
CHARGING PORTS / AMPS	2.4A
CHARGING METHOD	USB
CONNECTOR TYPE	Power USB/Thunderbolt/Lightning
INPUT NOMINAL VOLTAGE	230 VAC 120 VAC
PRODUCT FEATURES	C7 to BS-1363 Overcurrent Protection Overvoltage Protection
PACKAGE CONTENTS	U280-004-UK 4-Port USB Charging Station C7 to BS-1363 power cord, 1.2 m Quick Start Guide
PRODUCT HIGHLIGHTS	5V, 1.5A per port simultaneously when at maximum capacity Internal dual-voltage power supply with BS-1363 plug

