



Eaton U280-010-ST

10-Port USB Charging Station with Adjustable Storage, 12V 8A (96W) USB Charger Output

□□□□

PRODUCT NAME	Eaton Tripp Lite series multi-device charger
CATALOG NUMBER	U280-010-ST
UPC	037332190352
PRODUCT LENGTH/DEPTH	5.276 in
PRODUCT HEIGHT	0.984 in
PRODUCT WIDTH	9.37 in
PRODUCT WEIGHT	0.57 lb
COMPLIANCES	FCC Class B CE Marked RoHS REACH
CERTIFICATIONS	EN 55024 EN 55022



Powering Business Worldwide



TYPE	Charging Station
AC ADAPTER	100-240V, 50/60Hz, 3A; Output: 12V, 8A, 3-ft.
AC POWER ADAPTER CORD LENGTH	3 ft
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V / 50/60Hz / 3A
AC POWER ADAPTER OUTPUT SPECS (V / A)	12V / 8A
CHARGING PORTS DETAILS	USB-A: Up to 5V/2.4A
NUMBER OF CHARGING PORTS	10
TOTAL CHARGING AMPS	19.2A
TOTAL CHARGING WATTS	96
POWER CONSUMPTION DETAIL	34W (Operating) 0.27W (Standby)
POWER CONSUMPTION	34 W
NUMBER OF PORTS	10
OVERLOAD PROTECTION	Yes
CHARGING METHOD DETAIL	USB-A: 5V/Max 2.4A Apple Fast Charge
LED INDICATORS	Blue (Power)
OPERATING TEMPERATURE RANGE	41° to 95°F (5° to 35°C)
STORAGE TEMPERATURE RANGE	-4° to 122°F (-20° to 50°C)
AC POWER ADAPTER PLUG(S)	NEMA 5-15P North America
RELATIVE HUMIDITY	20% to 80% RH, Non- Condensing
COLOR	Black
MATERIAL	Polycarbonate
CHARGING PORTS / AMPS	2.4A
CHARGING METHOD	USB
CONNECTOR TYPE	Power USB/Thunderbolt/Lightning
PRODUCT FEATURES	Overvoltage Protection Overcurrent Protection
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
PACKAGE CONTENTS	External Power Supply with C6 Inlet (Input: 100-240V, 50/60 Hz, 2A; Max Output: 12V, 8A, 3 ft.) 10-Port USB Charging

	<p>Station Owner's manual C5 to 5-15P Power Cord (14) Storage brackets</p>
PRODUCT HIGHLIGHTS	<p>Protects against overheating, overcurrent and overcharging Includes 14 adjustable storage brackets for organizing devices Up to 5V, 2.4A per port for charging battery-intensive devices Charges anywhere AC power is available—no computer required External dual-voltage power supply with NEMA 5-15P plug</p>
CHARGING FORM FACTOR	Charging hub
CHARGING PORT TYPE	USB A (FEMALE)
PACKAGING TYPE	Box
EXTERNAL POWER SUPPLY CERTIFICATIONS	<p>FCC PSE RoHS UL TUV GS CE CCC cUL</p>
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	USB A (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB A (FEMALE)
DEVICE COMPATIBILITY	<p>Amazon Kindle Phone Tablet</p>
CONNECTOR GROUP	<p>USB-A 5-15P</p>
CONNECTOR	<p>USB A (female) NEMA 5-15P</p>

