



Eaton U320-006-BK

USB 3.0 SuperSpeed A/A Cable (M/M), Black,
6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U320-006-BK
UPC	037332198730
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	0.5 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.2 lb
COMPLIANCES	RoHS

□□□□	
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR TYPE	USB/Thunderbolt/Lightning
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U320-006-BK USB 3.0 SuperSpeed A/A Cable (M/M)
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) Data flows both directions simultaneously Twisted 28/24 AWG data/power lines Backward compatible with earlier USB generations Supports data transfer rates up to 5 Gbps Nickel-plated connectors with gold-plated contacts
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (MALE)
OPERATING TEMPERATURE	14° to 122°F (-10° to 50°C)
OPERATING TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
STORAGE TEMPERATURE RANGE	5° to 140°F (-15° to 60°C)
SIDEB CONNECTOR3	USB 3.0 A (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	5 - 8ft (1 - 2M)
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CONNECTOR	USB 3.0 A (male)

□□
