



Eaton U322-006

USB 3.2 Gen 1 SuperSpeed Device Cable (A to B M/M), 6 ft. (1.83 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U322-006
UPC	037332154125
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.18 lb
COMPLIANCES	CE Marked RoHS REACH FCC Compliant

□□□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Blue
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.2 Gen 1 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	6 ft. USB 3.2 Gen 1 SuperSpeed A-B Device cable
PRODUCT HIGHLIGHTS	10 times faster than USB 2.0, with transfer rates up to 5 Gbps 6ft SuperSpeed USB 3.2 Gen 1 A-B Cable Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 B (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB 3.0 B (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	5 - 8ft (1 - 2M)
CABLE OUTER DIAMETER (OD)	5.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	USB-B USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CONNECTOR	USB 3.0 A (male) USB 3.0 B (male)

□□
