



Eaton U325-003-IND

USB 3.0 SuperSpeed A to A M/M Cable,
Industrial - IP68, Shielded, 3 ft. (0.91 m), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series Industrial cable
CATALOG NUMBER	U325-003-IND
UPC	037332209504
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9.7 in
PRODUCT WIDTH	6.9 in
PRODUCT WEIGHT	0.21 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS TAA Compliant
CERTIFICATIONS	UL Listed

	performance Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (MALE)
OPERATING TEMPERATURE	-4° to 176°F (-20° to 80°C)
OPERATING TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDEB CONNECTOR3	USB 3.0 A (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	5.5
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A
MATERIAL	PVC
PROTECTION RATING	IP68
TAA COMPLIANCE	Yes
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB 3.0 A (male)

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

