



Eaton U325-006-IND

USB 3.0 SuperSpeed A to A M/M Cable,
Industrial - IP68, Shielded, 6 ft. (1.83 m), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series Industrial cable
CATALOG NUMBER	U325-006-IND
UPC	037332209511
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9.7 in
PRODUCT WIDTH	6.9 in
PRODUCT WEIGHT	0.3 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS REACH TAA Compliant
CERTIFICATIONS	UL Listed

APPLICATION

- Connect process control, industrial production and diagnostic systems in factories, warehouses and other dusty environments
- Provide USB 3.0 connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops

OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	IP68 Rated Industrial Grade TAA Compliant
USB SPECIFICATION	USB 3.0 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U325-006-IND USB-A Male to USB-A Male Cable, SuperSpeed, 3.0/3.1, Industrial, 6 ft. (1.8 m)
PRODUCT HIGHLIGHTS	IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min. Lifetime limited warranty (Worldwide) Built to protect process control and other USB 3.0 applications in harsh environments Dispels EMI/RFI line noise that can destroy data and affect equipment performance Complies with Federal

