



Eaton U325-013-IND

USB 3.0 SuperSpeed A to A M/M Cable,
Industrial - IP68, Shielded, 13 ft. (3.96 m),
TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series Industrial cable
CATALOG NUMBER	U325-013-IND
UPC	037332209566
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10.7 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.6 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS TAA Compliant
CERTIFICATIONS	UL Listed

APPLICATION

- Connect process control, industrial production and diagnostic systems in factories, warehouses and other dusty environments
- Provide USB 3.0 connectivity in outdoor environments susceptible to rain, such as a stadium or outdoor arena
- Set up outdoor digital signage at malls, theaters and bus stops

OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	20% to 80% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	IP68 Rated Industrial Grade TAA Compliant
USB SPECIFICATION	USB 3.0 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U325-013-IND USB-A Male to USB-A Male Cable, SuperSpeed, 3.0/3.1, Industrial, 13-ft. (3.96 m)
PRODUCT HIGHLIGHTS	Built to protect process control and other USB 3.0 applications in harsh environments Supports USB 3.0 data transfer rates up to 5 Gbps—10x faster than USB 2.0 Complies with Federal Trade Agreements Act standards for GSA Schedule purchases Lifetime limited warranty (Worldwide) Dispels EMI/RFI line noise

	that can destroy data and affect equipment performance IP68-rated to resist dust and endure immersion in 1.5 m of water up to 60 min.
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 A (MALE)
OPERATING TEMPERATURE	-4° to 176°F (-20° to 80°C)
OPERATING TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDEB CONNECTOR3	USB 3.0 A (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	9 - 14ft (2 - 4M)
CABLE OUTER DIAMETER (OD)	6.2
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A
MATERIAL	PVC
PROTECTION RATING	IP68
TAA COMPLIANCE	Yes
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CONNECTOR	USB 3.0 A (male)

□□□□:
□□□□:
□□□:
□□: