



Eaton U326-003-BK

USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M) Black, 3 ft. (0.91 m)



PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U326-003-BK
UPC	037332183170
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.11 lb
COMPLIANCES	RoHS CE Marked REACH FCC Compliant



Powering Business Worldwide



RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.0 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	3-ft. SuperSpeed USB 3.0 A Male to Micro B Male Device Cable - Black
PRODUCT HIGHLIGHTS	10 times faster than USB 2.0, with transfer rates up to 5 Gbps 3-ft. SuperSpeed USB 3.0 A to Micro B Cable
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 MICRO-B (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB 3.0 MICRO-B (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	5.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	Micro USB USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB 3.0 A (male) USB 3.0 Micro-B (male)



