



Eaton U326-003

USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M), Blue, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U326-003
UPC	037332158123
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.06 lb
COMPLIANCES	REACH RoHS FCC Compliant CE Marked

□□□□	
RELATIVE HUMIDITY	10% to 85%, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Blue
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.0 (up to 5 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	3-ft. (0.91 m) USB 3.0 SuperSpeed A-Male to Micro-B Male
PRODUCT HIGHLIGHTS	Lifetime limited warranty (Worldwide) 10 times faster than USB 2.0, with transfer rates up to 5 Gbps 3-ft. (0.91 m) SuperSpeed USB 3.0 A to Micro-B Cable
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB 3.0 A (MALE)
SIDEB CONNECTOR1	USB 3.0 MICRO-B (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDEB CONNECTOR3	USB 3.0 MICRO-B (MALE)
TECHNOLOGY	USB 3.x
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	5.5MM
CABLE TYPE	Passive
CONNECTOR GROUP	Micro USB USB-A
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB 3.0 A (male) USB 3.0 Micro-B (male)

□□



© 2026 〇〇 〇〇〇〇〇〇〇〇