



Eaton U360-007-SW

7-Port USB-C Hub - USB 3.2 Gen 1 (5 Gbps)
USB-A Ports with On/Off Buttons, Optional
USB-A Adapter, Gray

□□□□

PRODUCT NAME	Eaton Tripp Lite series hub
CATALOG NUMBER	U360-007-SW
UPC	037332293978
PRODUCT LENGTH/DEPTH	1.95 in
PRODUCT HEIGHT	0.44 in
PRODUCT WIDTH	0.79 in
PRODUCT WEIGHT	0.39 lb
COMPLIANCES	CE Marked FCC Compliant REACH RoHS UKCA WEEE Directive
CERTIFICATIONS	EN 55032 CISPR 35/EN 55035 ICES

Specifications	
TYPE	Hub
CHARGING PORTS DETAILS	USB-A: All USB-A ports provide 5V 1.5A (7.5W) to connected devices
NUMBER OF CHARGING PORTS	7
TOTAL CHARGING WATTS	7.5
DEVICE COMPATIBILITY	Chromebook Computer Laptop Tablet
AC POWER ADAPTER PLUG(S)	AS/NZS 3112 Australia BS 1363 UK CEE 7/7 Schuko NEMA 1-15P North America
OPERATING HUMIDITY RANGE	10% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	10% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 95% RH, Non-Condensing
COLOR	Gray
MATERIAL	ABS
USB HUB PORTS	Yes
CABLE JACKET COLOR	Black
CHARGING PORTS / AMPS	1.5A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	Battery Charging (5V/1.5A Port)
USB SPECIFICATION	USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
PACKAGE CONTENTS	USB-C host cable with optional USB-A adapter, 3 ft. (0.9 m) Installation instructions External power supply (Input: 100–240V, 50/60 Hz, 0.6A; Output: 12V 2A 24W) with 5 ft. (1.5 m) cord U360-007-SW 7-Port USB-C Hub (4) International plug adapters (North America, U.K., Europe, Australia)
PRODUCT HIGHLIGHTS	Each port can be turned off when not in use for

	extra security and privacy Plug-and-play operation with no software required for immediate connection 3-year limited warranty (Worldwide) 7 USB-A ports support USB 3.2 Gen 1 speeds up to 5 Gbps for fast data transfers Accepts up to 7 USB peripherals, turning your computer into a mini workstation Slim housing fits easily into backpack or bag for convenient work-from- anywhere use
CHARGING PORT TYPE	USB A (FEMALE) USB C (FEMALE)
PACKAGING TYPE	Box
PLUG COLOR	White Blue
EXTERNAL POWER SUPPLY CERTIFICATIONS	C-Tick CCC CE DOE GS TUV UL WEEE cUL
POWER SOURCE TYPE	AC Adapter
SIDEA CONNECTOR1	USB A (FEMALE)
COMPATIBLE DEVICES	Chromebook Laptop Smartphone Tablet
SIDEB CONNECTOR1	USB C (FEMALE)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB A (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.5 x 10 mm, positive pin, negative sleeve
SIDEB CONNECTOR3	USB C (FEMALE)
VOLTAGE COMPATIBILITY (VAC)	100 VAC 110 VAC 120 VAC 125 VAC 127 VAC 200 VAC 208 VAC 220 VAC 230 VAC

	240
HOST CONNECTOR	USB C (FEMALE)
CHARGING AMPS PER PORT	1.5 A
TECHNOLOGY	Thunderbolt USB 3.x
CHARGING PORTS	USB-A: 5V 1.5A (7.5W)
DATA TRANSFER RATE	5 Gbps
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.6A; Output: 12V, 2A, 5 ft.
AC POWER ADAPTER INPUT SPECS (V / HZ / A)	100-240V, 50/60Hz, 0.6A
AC POWER ADAPTER OUTPUT SPECS (V / A)	12V, 2A
AC POWER ADAPTER CORD LENGTH	5 ft
NUMBER OF PORTS	7
NUMBER OF USB HUB PORTS	7
POWER CONSUMPTION	1.4 W
TOTAL NUMBER OF PORTS	8
LED INDICATORS	(x7) White (Connection)
OPERATING TEMPERATURE RANGE	32° to 122°F (0° to 50°C)
STORAGE TEMPERATURE RANGE	68° to 158°F (20° to 70°C)
CABLE OUTER DIAMETER (OD)	5.0mm
OVER CURRENT PROTECTION	Yes
POWER PROVIDED TO CONNECTED DEVICE(S)	5V 1.5A
WIRE GAUGE (AWG)	24/30/32
DATA PORTS DETAILS	USB-A - USB 3.2 Gen 1 (5 Gbps)

