



Eaton U420-C03-G2-5A

USB-C Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), 5A (100W) Rating, USB-IF Certified, Thunderbolt 3 Compatible, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U420-C03-G2-5A
UPC	037332214997
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.07 lb
COMPLIANCES	REACH RoHS CE Marked FCC Compliant
CERTIFICATIONS	USB-IF

APPLICATION

- Charge and sync a USB-C or Thunderbolt 3 mobile device from a USB-C wall charger up to 3 ft. away
- Transfer data between an external hard drive or flash drive and your laptop or computer
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port

RELATIVE HUMIDITY	10% to 85% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 3.1 Gen 2 (up to 10 Gbps)
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U420-C03-G2-5A USB-C to USB-C Cable, USB-IF, M/M, 3 ft.
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) USB-C to USB-C cable is compatible with all USB-C and Thunderbolt 3 devices Certified by USB-IF to ensure highest-grade construction and performance Provides 5A (100W) power output for charging, syncing and powering mobile devices Reversible USB-C plugs connect in either direction for immediate no-fuss use Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
CONTACT PLATING	Gold
SIDE A CONNECTOR ¹	USB C (MALE)

SIDE B CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 158°F (-20° to 70°C)
SIDE B CONNECTOR3	USB C (MALE)
TECHNOLOGY	USB 3.x Thunderbolt
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	5.2 mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-C
MATERIAL	PVC
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB C (male)
