



Eaton U428-003-G2

USB-C to USB-A Cable (M/M), USB 3.2 Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	U428-003-G2
UPC	037332197498
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.11 lb
COMPLIANCES	RoHS CE Marked REACH FCC Compliant
CERTIFICATIONS	ICES NOM



Powering Business Worldwide

DEVICE COMPATIBILITY	Tablet Phone Amazon Kindle Chromebook Computer Laptop
RELATIVE HUMIDITY	10 to 85% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CHARGING METHOD	USB
CONNECTOR TYPE	USB/Thunderbolt/Lightning
PRODUCT FEATURES	USB Charging
USB SPECIFICATION	USB 3.2 Gen 2 (Up to 10 Gbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	U428-003-G2 USB 3.2 Gen 2 (10 Gbps) Cable, USB-C to USB-A (M/M), 3 ft.
PRODUCT HIGHLIGHTS	Molded nickel-plated connectors and gold-plated contacts Backward compatible with previous USB generations Capable of charging a connected device with up to 60W (5~20V/3A) USB 3.2 Gen 2 data transfer speeds up to 10 Gbps Error-free signal quality and EMI/RFI protection
CONTACT PLATING	Gold
SIDE A CONNECTOR1	USB A (MALE)
COMPATIBLE DEVICES	Chromebook Laptop Smartphone Tablet
SIDE B CONNECTOR1	USB C (MALE)
OPERATING TEMPERATURE	14° to 140°F (-10° to 60°C)
OPERATING TEMPERATURE RANGE	14° to 140°F (-10° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 185°F (-20° to 85°C)
SIDE B CONNECTOR3	USB C (MALE)
TECHNOLOGY	

