



Eaton U444-06N-H4-C

USB-C to HDMI Adapter with PD Charging,
HDCP, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series multi-port adapter
CATALOG NUMBER	U444-06N-H4-C
UPC	037332193926
PRODUCT LENGTH/DEPTH	1.57 in
PRODUCT HEIGHT	0.45 in
PRODUCT WIDTH	1.7 in
PRODUCT WEIGHT	0.2 lb
COMPLIANCES	RoHS FCC Compliant REACH CE Marked

- APPLICATION
- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television or projector
 - Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
 - Charge and power a USB-C or Thunderbolt 3 device with its AC wall charger
 - Connect a USB peripheral, such as an external hard drive, printer or hub

TYPE	USB-C Multiport Adapter
CHARGING PORTS DETAILS	Provides up to 60W (20V/3A) of power to the host device via the PD Charging port
NUMBER OF CHARGING PORTS	1
TOTAL CHARGING AMPS	3
TOTAL CHARGING WATTS	60
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	5% to 90% RH, Non-Condensing
COLOR	White
MATERIAL	PVC, ABS
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CABLE JACKET COLOR	White
CHARGING PORTS / AMPS	3A
CONNECTOR PLATING	Nickel
PRODUCT FEATURES	Mirror Mode 3D Video Supported Extended Mode DisplayPort Alt Mode Bus Powered

USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
CABLE JACKET MATERIAL	PVC
PACKAGE CONTENTS	Owner's manual U444-06N-H4-C USB 3.2 Gen 1 USB-C to HDMI 4K Adapter
PRODUCT HIGHLIGHTS	Plug-and-play operation with no software or drivers required Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers Transmits video signals from sources supporting USB DisplayPort Alt Mode 3-year limited warranty (Worldwide) USB-C PD charging port supports power input up to 20V 3A (60W) Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
CHARGING PORT TYPE	USB C (FEMALE)
PACKAGING TYPE	Box
PLUG COLOR	White Blue
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
HOST CONNECTOR	USB C (MALE)
CHARGING AMPS PER PORT	3 A
TECHNOLOGY	HDMI
CHARGING PORTS	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
VIDEO PORTS DETAILS	• HDMI 1.4 • HDCP 1.4 • DisplayPort 1.2
SUPPORTED RESOLUTION	1280x720 (720p) 1920x1080 (1080p) 3840x2160 (4K)
NUMBER OF DISPLAYS	1
NUMBER OF USB HUB PORTS	0

NUMBER OF MONITORS SUPPORTED	1
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K x 2K) @ 30Hz
VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI (FEMALE) HDCP 1.4 DisplayPort 1.2 HDMI 1.4
USB POWER DELIVERY (PD) CHARGING SPECIFICATION	20V/3A 60W
