



Eaton U444-06N-H4UB-C

USB-C to HDMI 4K Adapter with USB-A Port and PD Charging, HDCP, Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series USB adapter
CATALOG NUMBER	U444-06N-H4UB-C
UPC	037332210678
PRODUCT LENGTH/DEPTH	2.32 in
PRODUCT HEIGHT	0.55 in
PRODUCT WIDTH	1.57 in
PRODUCT WEIGHT	0.09 lb
COMPLIANCES	REACH CE Marked FCC Compliant RoHS

APPLICATION

- Stream video from your laptop to a 4K TV
- Give a video presentation at a meeting, training session, conference or trade show
- Add a second, large-screen monitor to your laptop

TYPE	USB-C Multiport Adapter
RELATIVE HUMIDITY	10% to 85% RH
COLOR	Black
USB HUB PORTS	Yes
USB POWER DELIVERY (PD) CHARGING SUPPORT	Yes
CHARGING PORTS / AMPS	1.5A 3A
CONNECTOR PLATING	Nickel
CHARGING METHOD	USB
PRODUCT FEATURES	DisplayPort Alt Mode Bus Powered Extended Mode 3D Video Supported Mirror Mode USB Charging Battery Charging (5V/1.5A Port)
USB SPECIFICATION	USB 3.0 (up to 5 Gbps) USB 3.1 Gen 1 (up to 5 Gbps) USB 3.2 Gen 1 (up to 5 Gbps)
PRODUCT HIGHLIGHTS	Transmits video signals from sources supporting USB DisplayPort Alt Mode Easy installation with plug-and-play operation—no software required Reversible USB-C plug connects in either direction for immediate no-fuss use Supports USB 3.1 Gen 1 speeds up to 5 Gbps to ensure fast data transfers Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz

CHARGING PORT TYPE	USB A (FEMALE) USB C (FEMALE)
CHROMA SUB SAMPLING	4:4:4
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	USB C (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
OPERATING TEMPERATURE	32° to 113°F (0° to 45°C)
OPERATING TEMPERATURE RANGE	32° to 113°F (0° to 45°C)
STORAGE TEMPERATURE RANGE	14° to 158°F (-10° to 70°C)
DATA PORTS	USB-A - USB 3.2 Gen 1 (5 Gbps) USB-C - USB 3.2 Gen 1 (5 Gbps) USB C (FEMALE) USB A (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
SIDEB CONNECTOR4	USB A (FEMALE)
HOST CONNECTOR	USB C (MALE)
SIDEB CONNECTORS5	USB C (FEMALE)
CHARGING AMPS PER PORT	1.5 A 3 A 3A
TECHNOLOGY	HDMI USB 3.x
CHARGING PORTS	USB-A: 5V 1.5A (7.5W) USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
VIDEO PORTS DETAILS	<ul style="list-style-type: none">• HDMI 1.4• HDCP 1.4
NUMBER OF CHARGING PORTS	2
BUILT-IN CABLE LENGTH	0.36 ft
NUMBER OF MONITORS SUPPORTED	1
NUMBER OF PORTS	3
NUMBER OF USB HUB PORTS	2
DATA PORTS DETAILS	<ul style="list-style-type: none">• USB-A - USB 3.2 Gen 1 (5 Gbps)• USB-C - USB 3.2 Gen 1 (5 Gbps)
MATERIAL	PVC, ABS

MAX SUPPORTED COLOR DEPTH	36-bit Deep Color
MAX SUPPORTED VIDEO RESOLUTION	HDMI: 3840 x 2160 (4K x 2K) @ 30Hz
POWER PROVIDED TO CONNECTED DEVICE(S)	5% to 90% RH
TOTAL CHARGING AMPS	3
TOTAL CHARGING WATTS	60 W
VIDEO INPUT	USB C (MALE)
VIDEO OUTPUT	HDMI (FEMALE)
VIDEO PORTS	HDMI (FEMALE) HDMI 1.4 HDCP 1.4

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

