



Eaton ULCF30004GNC

Eaton ULCF3000 panel: Cooper, Addressable, Control Panels, Large System, UL Systems, 4 Loops, Network Card

□□□□

PRODUCT NAME	Eaton ULCF3000 panel
CATALOG NUMBER	ULCF30004GNC
PRODUCT LENGTH/DEPTH	205 mm
PRODUCT HEIGHT	395 mm
PRODUCT WIDTH	495 mm
PRODUCT WEIGHT	22.169 kg
CERTIFICATIONS	UL



Powering Business Worldwide

MOUNTING METHOD	Surface mounting
NUMBER OF DETECTION GROUPS	96
NUMBER OF OUTPUTS FOR ACOUSTIC SIGNAL GENERATORS	4
NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS	4
NUMBER OF DETECTOR ADDRESSES	200
OPERATING VOLTAGE	24 V
NUMBER OF BATTERIES	2
BATTERY VOLTAGE	12 V
BATTERY CAPACITY	7 Ah
CLASS CHANGE CAPABILITY	Yes
CONSTRUCTION MATERIAL BACK ENCLOSURE	Mild steel
CONSTRUCTION MATERIAL FRONT ENCLOSURE	ABS
HUMIDITY (NON CONDENSING) - MAX	75 %
HUMIDITY (NON CONDENSING) - MIN	0 %
INGRESS PROTECTION	IP30
MAXIMUM NUMBER OF ADDRESSABLE LOOPS	4
OPERATING TEMPERATURE - MAX	40 °C
OPERATING TEMPERATURE - MIN	-5 °C
SYSTEM TOPOLOGY	Addressable
MAXIMUM NETWORK SIZE (NUMBER OF NODES)	126
WEIGHT (WITHOUT BATTERIES)	16.8 kg
TYPE OF DISPLAY	Touchscreen
AUXILIARY FREE OUTPUT	Yes
AUXILIARY RELAYS	Fire/Fault
PRODUCT BRANDING	Eaton Cooper
SUITABLE FOR	Bus Connection
INTEGRATED FUNCTION	Interface External Emergency Power Supply

