



## Eaton ULDF60004GNC

Eaton ULCF3000 panel: Menvier,  
Addressable, Control Panels, Large System,  
UL Systems, 4 Loops, Network Card

□□□□

<b>PRODUCT NAME</b>	Eaton ULCF3000 panel
<b>CATALOG NUMBER</b>	ULDF60004GNC
<b>PRODUCT LENGTH/DEPTH</b>	210 mm
<b>PRODUCT HEIGHT</b>	397 mm
<b>PRODUCT WIDTH</b>	497 mm
<b>PRODUCT WEIGHT</b>	22.169 kg
<b>COMPLIANCES</b>	EN



Powering Business Worldwide



<b>MOUNTING METHOD</b>	Surface mounting
<b>NUMBER OF DETECTION GROUPS</b>	96
<b>NUMBER OF OUTPUTS FOR ACOUSTIC SIGNAL GENERATORS</b>	4
<b>NUMBER OF OUTPUTS FOR OPTICAL SIGNAL GENERATORS</b>	4
<b>NUMBER OF DETECTOR ADDRESSES</b>	200
<b>OPERATING VOLTAGE</b>	24 V
<b>NUMBER OF BATTERIES</b>	2
<b>BATTERY VOLTAGE</b>	12 V
<b>BATTERY CAPACITY</b>	7 Ah
<b>CLASS CHANGE CAPABILITY</b>	Yes
<b>CONSTRUCTION MATERIAL BACK ENCLOSURE</b>	Mild steel
<b>CONSTRUCTION MATERIAL FRONT ENCLOSURE</b>	ABS
<b>HUMIDITY (NON CONDENSING) - MAX</b>	75 %
<b>HUMIDITY (NON CONDENSING) - MIN</b>	0 %
<b>INGRESS PROTECTION</b>	IP30
<b>MAIN INPUT SUPPLY</b>	120 Vac, 60 Hz
<b>MAXIMUM NUMBER OF ADDRESSABLE LOOPS</b>	4
<b>OPERATING TEMPERATURE - MAX</b>	40 °C
<b>OPERATING TEMPERATURE - MIN</b>	-5 °C
<b>SYSTEM TOPOLOGY</b>	Addressable
<b>MAXIMUM NETWORK SIZE (NUMBER OF NODES)</b>	126
<b>WEIGHT (WITHOUT BATTERIES)</b>	16.8 kg
<b>TYPE OF DISPLAY</b>	Touchscreen
<b>AUXILIARY FREE OUTPUT</b>	Yes
<b>AUXILIARY RELAYS</b>	Fire/Fault
<b>PRODUCT BRANDING</b>	Eaton Menvier
<b>SUITABLE FOR</b>	Bus Connection

