



Eaton UNJC232

Eaton Crouse-Hinds series UNJC flexible fixture hanger, 24-48 lb, 3/4" luminaire stem size, Malleable iron, Pendant mount, 3/4" nipple size, Cushion type

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series UNJC flexible fixture hanger
CATALOG NUMBER	UNJC232
UPC	782274647104
PRODUCT LENGTH/DEPTH	8.5 in
PRODUCT HEIGHT	3.53 in
PRODUCT WIDTH	5.2 in
PRODUCT WEIGHT	1.83 lb

Certifications and compliances	
AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2

UL	
UL E9000	Eaton Specification Sheet - UNJC232
UL E9000	Crouse-Hinds series Ball or Cushion Hazardous Area Flexible Fixture Hangers catalog page
UL E9000	Ball or Cushion Hazardous Area Flexible Fixture Hangers UL certification
UL E9000	Ball or Cushion Hazardous Area Flexible Fixture Hangers Canadian certification

UL E9000:
UL E9000:
UL E9000:
UL E9000:

Product specifications	
TYPE	Cushion
MOUNTING TYPE	Pendant
LUMINAIRE STEM SIZE	3/4"
NIPPLE SIZE	3/4"
LUMINAIRE RATED WEIGHT	24-48 lb
MATERIAL	Malleable iron