



## Eaton UR030-001

Universal Reversible USB 2.0 Converter Adapter Cable (Reversible A to 5Pin Mini B M/M), 1 ft. (0.31 m)

□□□□

<b>PRODUCT NAME</b>	Eaton Tripp Lite series cable
<b>CATALOG NUMBER</b>	UR030-001
<b>UPC</b>	037332182104
<b>PRODUCT LENGTH/DEPTH</b>	9 in
<b>PRODUCT HEIGHT</b>	0.25 in
<b>PRODUCT WIDTH</b>	0.25 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>COMPLIANCES</b>	RoHS



Powering Business Worldwide



<b>OPERATING HUMIDITY RANGE</b>	0% to 90% RH, Non-Condensing
<b>STORAGE HUMIDITY RANGE</b>	0% to 90% RH, Non-Condensing
<b>CABLE JACKET COLOR</b>	Black
<b>CONNECTOR TYPE</b>	USB/Thunderbolt/Lightning
<b>CONNECTOR STYLE</b>	Straight
<b>PACKAGE CONTENTS</b>	1-ft. (0.31 m) USB2.0 Universal / Reversible A to Mini-B Device Cable (A Male to 5Pin Mini-B Male)
<b>PRODUCT HIGHLIGHTS</b>	Universal / Reversible A connector eliminates guess-work as to connector orientation Meets or Exceeds USB 2.0 Specifications Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors
<b>SIDEA CONNECTOR1</b>	REVERSIBLE USB A (MALE)
<b>SIDEB CONNECTOR1</b>	USB MINI-B 5-PIN (MALE)
<b>OPERATING TEMPERATURE</b>	14° to 122°F (-10° to 50°C)
<b>OPERATING TEMPERATURE RANGE</b>	14° to 122°F (-10° to 50°C)
<b>STORAGE TEMPERATURE RANGE</b>	5° to 140°F (-15° to 60°C)
<b>SIDEB CONNECTOR3</b>	USB MINI-B 5-PIN (MALE)
<b>TECHNOLOGY</b>	USB 2.0 (High Speed)
<b>CABLE LENGTH</b>	Up to 4ft (up to 1M)
<b>CABLE TYPE</b>	Passive
<b>CONNECTOR GROUP</b>	USB Mini USB-B
<b>CABLE LENGTH RANGE</b>	Up to 4ft (up to 1M)
<b>CONNECTOR</b>	USB Mini-B 5-pin (male) USB A reversible (male)



