



□□□□□

Eaton UT062238SZH

Female plug IP68/69K, 48 h salt spray,
keying Z; UT062238SZH

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT062238SZH
PRODUCT LENGTH/DEPTH	27.3 mm
PRODUCT HEIGHT	42 mm
PRODUCT WIDTH	42 mm
PRODUCT WEIGHT	50.5 g
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

□□□□

□□

CURRENT RATING	5 A UL 6 A IEC
FITTED WITH:	Last mate first break capability(optional) Shielding First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire & Smoke Flammability rating UL94 V0 Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 REACH RoHS
ENVIRONMENTAL RESISTANCE	Vibrations level 2g per NFF61030 Resistant against mineral oil Resistant against gasoline Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against basic bath Resistant against acid bath Resistant against oil Shock resistance 30g, 18ms per NFF61030 Shock resistance 50g, 11ms per MIL-C-26482 I
TEST CURRENT	6 A IEC 3 A CSA 5 A UL
TEST VOLTAGE	500 V CSA 150 V IEC 500 V UL
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	38
PLATING	Nickel
PLUG TYPE	Straight Plug

SHELL MATERIAL	Zinc alloy
SHELL SIZE	22
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	38
NUMBER OF CAVITY #16	38
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

