

Eaton UT06FC128SH

Female plug with flexible conduit backshell, IP68/69K, 48 h salt spray; UT06FC128SH

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06FC128SH
PRODUCT LENGTH/DEPTH	60.9 mm
PRODUCT HEIGHT	26.1 mm
PRODUCT WIDTH	26.1 mm
PRODUCT WEIGHT	28.9 g
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 RoHS Fire & Smoke Flammability rating UL94 V0 REACH
ENVIRONMENTAL RESISTANCE	Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against acid bath Resistant against oil Resistant against mineral oil Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against basic bath Shock resistance 30g, 18ms per NFF61030 Resistant against gasoline Vibrations level 2g per NFF61030
TEST CURRENT	10 A UL 7 A CSA 10 A IEC
TEST VOLTAGE	125 V IEC 500 V CSA 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

