



Eaton UT06FC128SWH

Female plug with flexible conduit backshell,
IP68/69K, 48 h salt spray, keying W;
UT06FC128SWH

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06FC128SWH
PRODUCT LENGTH/DEPTH	60.9 mm
PRODUCT HEIGHT	26.1 mm
PRODUCT WIDTH	26.1 mm
PRODUCT WEIGHT	28.9 g
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

□□□□

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke Flammability rating UL94 V0 RoHS REACH
ENVIRONMENTAL RESISTANCE	Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against oil Resistant against mineral oil Resistant against basic bath Shock resistance 30g, 18ms per NFF61030 Vibrations level 2g per NFF61030 Resistant against acid bath Resistant against gasoline
TEST CURRENT	10 A IEC 7 A CSA 10 A UL
TEST VOLTAGE	125 V IEC 500 V UL 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
PLATING	Nickel

□□

PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

