

Eaton UT06FC2235SYH

Female plug with flexible conduit backshell,
IP68/69K, 48 h salt spray, keying Y;
UT06FC2235SYH

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06FC2235SYH
PRODUCT LENGTH/DEPTH	71.1 mm
PRODUCT HEIGHT	42 mm
PRODUCT WIDTH	42 mm
PRODUCT WEIGHT	61.7 g
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	6 A IEC 5 A UL
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 RoHS Fire & Smoke Flammability rating UL94 V0 REACH
ENVIRONMENTAL RESISTANCE	Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against acid bath Resistant against oil Resistant against basic bath Resistant against gasoline Vibrations level 2g per NFF61030 Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil Shock resistance 50g, 11ms per MIL-C-26482 I
TEST CURRENT	6 A IEC 5 A UL 3 A CSA
TEST VOLTAGE	500 V UL 150 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
LAYOUT	35
PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	22
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	35
NUMBER OF CAVITY #16	35
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

