

Eaton UT06GN104SH02

Female plug with single wire backshell,
IP68/69K, 96 h salt spray; UT06GN104SH02

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06GN104SH02
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	13 A IEC 10 A UL
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	REACH Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke RoHS Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against basic bath Vibrations level 2g per NFF61030 Resistant against oil Shock resistance 30g, 18ms per NFF61030 Resistant against gasoline Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against mineral oil Resistant against acid bath
TEST CURRENT	10 A UL 13 A IEC 7 A CSA
TEST VOLTAGE	150 V IEC 500 V UL 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide



LAYOUT	4
PLATING	Black Anodized
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

