

Eaton

UT06GN104SWH02

Female plug with single wire backshell,
IP68/69K, 96 h salt spray, keying W;
UT06GN104SWH02

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06GN104SWH02
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	10 A UL 13 A IEC
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 RoHS REACH Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 Fire & Smoke
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline Shock resistance 30g, 18ms per NFF61030 Resistant against acid bath Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against basic bath Resistant against mineral oil Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Vibrations level 2g per NFF61030
TEST CURRENT	10 A UL 7 A CSA 13 A IEC
TEST VOLTAGE	500 V UL 150 V IEC 500 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
LAYOUT	4
PLATING	Black Anodized
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

