

Eaton

UT06GN128PWH02

Male plug with single wire backshell,
IP68/69K, 96 h salt spray, keying W;
UT06GN128PWH02

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT06GN128PWH02
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977



Powering Business Worldwide

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	Last mate first break capability(optional) First mate last break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire & Smoke RoHS REACH Flammability rating UL94 V0 Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545
ENVIRONMENTAL RESISTANCE	Vibrations level 2g per NFF61030 Resistant against gasoline Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against oil Resistant against acid bath Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil Resistant against basic bath
TEST CURRENT	10 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	500 V CSA 125 V IEC 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68



INSERT MATERIAL	Polyamide
PLATING	Black Anodized
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

