

Eaton UT07GN104SWH

Female jam nut receptacle with single wire backshell, IP67, 48 h salt spray, keying W; UT07GN104SWH

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN104SWH
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	13 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 Fire & Smoke RoHS REACH Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against basic bath Resistant against acid bath Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 2g per NFF61030 Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil
TEST CURRENT	10 A UL 13 A IEC 7 A CSA
TEST VOLTAGE	500 V CSA 500 V UL 150 V IEC
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67



INSERT MATERIAL	Polyamide
LAYOUT	4
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

