

Eaton

UT07GN128PWH01

Male jam nut receptacle with single wire backshell, IP67, 96 h salt spray, keying W; UT07GN128PWH01

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT07GN128PWH01
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	10 A IEC 10 A UL
FITTED WITH:	First mate last break capability(optional) Last mate first break capability(optional)
ENVIRONMENTAL CONDITIONS	Fire & Smoke Flammability rating UL94 V0 Fire and smoke rating HL2 R22 and HL2 R23 following EN 45 545 REACH RoHS
ENVIRONMENTAL RESISTANCE	Shock resistance 50g, 11ms per MIL-C-26482 I Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against oil Resistant against basic bath Resistant against gasoline Shock resistance 30g, 18ms per NFF61030 Resistant against mineral oil Vibrations level 2g per NFF61030 Resistant against acid bath
TEST CURRENT	10 A UL 10 A IEC 7 A CSA
TEST VOLTAGE	500 V CSA 125 V IEC 500 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Single wire Backshell
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
INSERT MATERIAL	Polyamide



LAYOUT	8
PLATING	Nickel
SHELL MATERIAL	Zinc alloy
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

