



□□□□□

Eaton UT0W61626SH

Female plug IP68/69K, 48 h salt spray;
UT0W61626SH

□□□□

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT0W61626SH
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	32.4 mm
PRODUCT WIDTH	32.4 mm
PRODUCT WEIGHT	28.7 g
COMPLIANCES	Overvoltage category III / pollution degree III UL 1977

CURRENT RATING	4 A IEC 4 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	Fire & Smoke RoHS REACH Flammability rating UL94 V0
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline Resistant against basic bath Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against acid bath Resistant against mineral oil Shock resistance 50g, 11ms per MIL-C-26482 I
TEST CURRENT	4 A IEC 4 A UL 3 A CSA
TEST VOLTAGE	250 V CSA 250 V UL 40 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	26
PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	16
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	26

NUMBER OF CAVITY #20	26
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

