

# Eaton UT0W6FC1626SH

Female plug with flexible conduit backshell, IP68/69K, 48 h salt spray; UT0W6FC1626SH

<b>PRODUCT NAME</b>	Eaton Souriau UTO series metal IP68/69k connector for intensive use
<b>CATALOG NUMBER</b>	UT0W6FC1626SH
<b>PRODUCT LENGTH/DEPTH</b>	69.2 mm
<b>PRODUCT HEIGHT</b>	32.4 mm
<b>PRODUCT WIDTH</b>	32.4 mm
<b>PRODUCT WEIGHT</b>	37.8 g
<b>COMPLIANCES</b>	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	4 A IEC 4 A UL
ENVIRONMENTAL CONDITIONS	Fire & Smoke RoHS Flammability rating UL94 V0 REACH
ENVIRONMENTAL RESISTANCE	Resistant against acid bath
	Resistant against oil Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against gasoline Resistant against basic bath Resistant against mineral oil Shock resistance 50g, 11ms per MIL-C-26482 I
TEST CURRENT	4 A UL 3 A CSA 4 A IEC
TEST VOLTAGE	40 V IEC 250 V CSA 250 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	26
PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	16
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C



<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF CONTACTS</b>	26
<b>NUMBER OF CAVITY #20</b>	26
<b>SALT SPRAY</b>	48 hour

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

