

Eaton

UT0W6FC2461SWH

Female plug with flexible conduit backshell,
IP68/69K, 48 h salt spray, keying W;
UT0W6FC2461SWH

PRODUCT NAME	Eaton Souriau UTO series metal IP68/69k connector for intensive use
CATALOG NUMBER	UT0W6FC2461SWH
PRODUCT LENGTH/DEPTH	70.9 mm
PRODUCT HEIGHT	45 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	61.8 g
COMPLIANCES	UL 1977 Overvoltage category III / pollution degree III

CURRENT RATING	3 A IEC 3 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 V0 REACH Fire & Smoke
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Vibrations level 55-2000 Hz, 15g per MIL-C-26482 I Resistant against oil Resistant against acid bath Resistant against basic bath Shock resistance 50g, 11ms per MIL-C-26482 I Resistant against gasoline
TEST CURRENT	2 A CSA 3 A IEC 3 A UL
TEST VOLTAGE	250 V UL 80 V IEC 250 V CSA
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	For Flexible Conduit
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	61
PLATING	Nickel
PLUG TYPE	Straight Plug
SHELL MATERIAL	Zinc alloy
SHELL SIZE	24
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C



OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	61
NUMBER OF CAVITY #20	61
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

