



# Eaton UTG1103SVDE

Female free hanging receptacle;  
UTG1103SVDE

<b>PRODUCT NAME</b>	Eaton Souriau UTG series metal and plastic connector for heavy use
<b>CATALOG NUMBER</b>	UTG1103SVDE



<b>FITTED WITH:</b>	Layout with ground cavity First mate last break capability Last mate first break capability
<b>ENVIRONMENTAL CONDITIONS</b>	REACH Flammability rating UL94 V0 RoHS
<b>CONNECTOR ACCESSORY OPTION</b>	Not delivered, to be ordered separately
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Not delivered
<b>CONTACT GENDER</b>	Socket (Female)
<b>CONTACT TYPE</b>	Crimp
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP65
<b>INSERT MATERIAL</b>	Polyamide
<b>LAYOUT</b>	3
<b>SHELL MATERIAL</b>	Metal & Plastic
<b>SHELL SIZE</b>	10
<b>MATING CYCLES</b>	500
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>RECEPTACLE TYPE</b>	In-Line Receptacle
<b>NUMBER OF CONTACTS</b>	3
<b>NUMBER OF CAVITY #16</b>	3
<b>SALT SPRAY</b>	48 hour

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
: