

Eaton UTGX0102W2P

Square flange receptacle, without backshell,
for 4 male contacts, IP68/69K;
UTGX0102W2P

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX0102W2P
PRODUCT LENGTH/DEPTH	39.7 mm
PRODUCT HEIGHT	23.8 mm
PRODUCT WIDTH	23.8 mm
PRODUCT WEIGHT	6 g

**ENVIRONMENTAL
CONDITIONS**

REACH
RoHS
Flammability rating UL94
V0

**CONNECTOR ACCESSORY
OPTION**

No backshell possibility

**CONNECTOR
ORIENTATION**

N

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Not delivered

CONTACT GENDER

Pin (Male)

CONTACT TYPE

Crimp

COUPLING TYPE

1/3 Bayonet

LAYOUT

2W2

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

10

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

Square Flange Receptacle

NUMBER OF CONTACTS

4

NUMBER OF CAVITY #20

2

SALT SPRAY

500 hour

3D[utgx0102w2p.stp](#)**PROJECT NAME:****PROJECT NUMBER:****PREPARED BY:**

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

