

Eaton UTGX010D98PW

Square flange receptacle, without backshell, with 6 male PCB contacts, IP68/69K in unmated conditions, keying W; UTGX010D98PW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX010D98PW
PRODUCT LENGTH/DEPTH	32.3 mm
PRODUCT HEIGHT	23.8 mm
PRODUCT WIDTH	23.8 mm
PRODUCT WEIGHT	9 g

**ENVIRONMENTAL
CONDITIONS**

Flammability rating UL94
V0
RoHS
REACH

**CONNECTOR ACCESSORY
OPTION**

No backshell possibility

**CONNECTOR
ORIENTATION**

W

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Loaded

CONTACT GENDER

Pin (Male)

CONTACT TYPE

PCB

COUPLING TYPE

1/3 Bayonet

LAYOUT

D98

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

10

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

Square Flange Receptacle

NUMBER OF CONTACTS

6

NUMBER OF CAVITY #20

3

SALT SPRAY

500 hour

3D[utgx010d98pw.stp](#)**PROJECT NAME:****PROJECT NUMBER:****PREPARED BY:**

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

