



□□□□

Eaton UTGX012D4S

Square flange receptacle, without backshell, with 4 female PCB contacts, IP68/69K in unmated conditions; UTGX012D4S

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX012D4S
PRODUCT LENGTH/DEPTH	32.3 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	11 g

0000	
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
LAYOUT	D4
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:

00	3D 00	utgx012d4s.stp
----	-------	--------------------------------