



□□□□□

Eaton UTGX012E14P

Square flange receptacle, without backshell, with 14 male solder contacts, IP68/69K in unmated conditions; UTGX012E14P

□□□□

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX012E14P
PRODUCT LENGTH/DEPTH	32.3 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	9 g

0000	
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E14
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	12
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	14
NUMBER OF CAVITY #20	14
SALT SPRAY	500 hour

00	
3D 00	utgx012e14p.stp

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00: