

Eaton UTGX014D12P

Square flange receptacle, without backshell, with 12 male PCB contacts, IP68/69K in unmated conditions; UTGX014D12P

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX014D12P
PRODUCT LENGTH/DEPTH	32.3 mm
PRODUCT HEIGHT	28.6 mm
PRODUCT WIDTH	28.6 mm
PRODUCT WEIGHT	13 g

ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 V0 RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
LAYOUT	D12
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	14
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: