

Eaton UTGX0JC104SW

Square flange receptacle, with cable gland backshell, for 4 female contacts, IP68/69K, keying W; UTGX0JC104SW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX0JC104SW
PRODUCT LENGTH/DEPTH	78.4 mm
PRODUCT HEIGHT	23.8 mm
PRODUCT WIDTH	23.8 mm
PRODUCT WEIGHT	16 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94
	V0
	RoHS
	REACH
BACKSHELL ANGLE	straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
LAYOUT	4
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

