

Eaton UTGX0JC106PW

Square flange receptacle, with cable gland backshell, for 6 male contacts, IP68/69K, keying W; UTGX0JC106PW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX0JC106PW
PRODUCT LENGTH/DEPTH	78.4 mm
PRODUCT HEIGHT	23.8 mm
PRODUCT WIDTH	23.8 mm
PRODUCT WEIGHT	16 g

ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
--------------------------	--

BACKSHELL ANGLE	straight
-----------------	----------

BACKSHELL TYPE	Sealing Gland
----------------	---------------

CONNECTOR ACCESSORY OPTION	Delivered with connector
----------------------------	--------------------------

CONNECTOR ORIENTATION	W
-----------------------	---

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Pin (Male)
----------------	------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

LAYOUT	6
--------	---

SHELL MATERIAL	Metal & Plastic
----------------	-----------------

SHELL SIZE	10
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	105 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

RECEPTACLE TYPE	Square Flange Receptacle
-----------------	--------------------------

NUMBER OF CONTACTS	6
--------------------	---

NUMBER OF CAVITY #20	6
----------------------	---

SALT SPRAY	500 hour
------------	----------

3D

[utgx0jc106pw.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

