

Eaton UTGX1JC104P

In line receptacle, with cable gland backshell, for 4 male contacts, IP68/69K; UTGX1JC104P

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX1JC104P
PRODUCT LENGTH/DEPTH	70 mm
PRODUCT HEIGHT	26.7 mm
PRODUCT WIDTH	26.7 mm
PRODUCT WEIGHT	16 g

ENVIRONMENTAL CONDITIONS	REACH
	Flammability rating UL94
	V0
	RoHS
BACKSHELL ANGLE	straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
LAYOUT	4
SHELL MATERIAL	Metal & Plastic
SHELL SIZE	10
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	In-Line Receptacle
NUMBER OF CONTACTS	4
NUMBER OF CAVITY #16	4
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: