

## Eaton UTGX1JC104PW

In line receptacle, with cable gland backshell, for 4 male contacts, IP68/69K, keying W; UTGX1JC104PW

<b>PRODUCT NAME</b>	Eaton Souriau UTGX series ruggedized connectors for harsh environments
<b>CATALOG NUMBER</b>	UTGX1JC104PW
<b>PRODUCT LENGTH/DEPTH</b>	70 mm
<b>PRODUCT HEIGHT</b>	26.7 mm
<b>PRODUCT WIDTH</b>	26.7 mm
<b>PRODUCT WEIGHT</b>	16 g

<b>ENVIRONMENTAL CONDITIONS</b>	REACH
	Flammability rating UL94
	V0
	RoHS
<b>BACKSHELL ANGLE</b>	straight
<b>BACKSHELL TYPE</b>	Sealing Gland
<b>CONNECTOR ACCESSORY OPTION</b>	Delivered with connector
<b>CONNECTOR ORIENTATION</b>	W
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Not delivered
<b>CONTACT GENDER</b>	Pin (Male)
<b>CONTACT TYPE</b>	Crimp
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>LAYOUT</b>	4
<b>SHELL MATERIAL</b>	Metal & Plastic
<b>SHELL SIZE</b>	10
<b>MATING CYCLES</b>	500
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>RECEPTACLE TYPE</b>	In-Line Receptacle
<b>NUMBER OF CONTACTS</b>	4
<b>NUMBER OF CAVITY #16</b>	4
<b>SALT SPRAY</b>	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

: