

Eaton UTGX1JC106SW

In line receptacle, with cable gland backshell, for 6 female contacts, IP68/69K, keying W; UTGX1JC106SW

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX1JC106SW
PRODUCT LENGTH/DEPTH	70 mm
PRODUCT HEIGHT	26.7 mm
PRODUCT WIDTH	26.7 mm
PRODUCT WEIGHT	16 g

**ENVIRONMENTAL
CONDITIONS**

RoHS
REACH
Flammability rating UL94
V0

BACKSHELL ANGLE

straight

BACKSHELL TYPE

Sealing Gland

**CONNECTOR ACCESSORY
OPTION**

Delivered with connector

**CONNECTOR
ORIENTATION**

W

CONNECTOR TYPE

Receptacle

CONTACT DELIVERY

Not delivered

CONTACT GENDER

Socket (Female)

CONTACT TYPE

Crimp

COUPLING TYPE

1/3 Bayonet

LAYOUT

6

SHELL MATERIAL

Metal & Plastic

SHELL SIZE

10

MATING CYCLES

500

**OPERATING
TEMPERATURE - MAX**

105 °C

**OPERATING
TEMPERATURE - MIN**

-40 °C

RECEPTACLE TYPE

In-Line Receptacle

NUMBER OF CONTACTS

6

NUMBER OF CAVITY #20

6

SALT SPRAY

500 hour

3D

[utgx1jc106sw.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

